




TJA470



IK04

IP20

Domovea expert

Technical Features

Equipment

Web server	Yes
------------	-----

Voltage

Operating voltage	24 - 24 V
Operating voltage over bus	21 - 32 V
Type voltage supply	DC

Connectivity

Type of interface bus system/media gateway	Multiple interface
--	--------------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Equipment

Number of channels	1
--------------------	---

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Controls and indicators

With LED indication	Yes
---------------------	-----

Dimensions

Number of width units	6
-----------------------	---

Texts

Encoding	Management of 4 configurable user profiles
Function	Local and remote connection of the door station with IP end devices, such as smartphones, tablet computers and PCs
Labelling	Large labelling field
Connectors jacks	With 2 USB sockets type A
Type of connection	With quickconnect plug-in terminals

Sustainability

RoHS conform	Yes
--------------	-----