



80164780



IP20



Push-button 4g, lab. field,RGB LED, int. temp.sensor, KNX-S.1/B.3/B.7,f.wh.p.wh.

Technical Features

Installation, mounting

Mounting on Flush mounting

Use conditions

Operating temperature -5 - 45 °C

Electric current

Bus current consumption data transfer 20 mA

Functions

With room temperature controller No

Dimensions

Height 55.30 mm

Width 55.80 mm

Depth 13.85 mm

Equipment

Number of actuation points 8

Controls and indicators

With LED indication Yes

Materials

Colour White

RAL code 1013

Material Thermoplastic

Surface finish Glossy

Accessories

Has labelling field Yes

Screen

With display No

Texts

Function Function for manual interruption of automatic functions already triggered

Protection With dismantling protection

Temperature Integrated temperature sensor with output of the measured values via object

Sustainability

REACH-SVHC free Yes

RoHS conform Yes