



TJA670



Domovea basic

Technical Features

Equipment

| | |
|------------|-----|
| Web server | Yes |
|------------|-----|

Voltage

| | |
|----------------------------|-----------|
| Operating voltage | 24 - 24 V |
| Operating voltage over bus | 21 - 32 V |
| Type voltage supply | DC |

Connectivity

| | |
|--|--------------------|
| Type of interface bus system/media gateway | Multiple interface |
|--|--------------------|

Settings

| | |
|------------------------------|----------|
| Supported configuration mode | ETS easy |
|------------------------------|----------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Equipment

| | |
|--------------------|---|
| Number of channels | 1 |
|--------------------|---|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

Controls and indicators

| | |
|---------------------|-----|
| With LED indication | Yes |
|---------------------|-----|

Dimensions

| | |
|-----------------------|-------------|
| Width | 105 mm |
| Dimensions | 90 x 105 mm |
| Depth | 65 mm |
| Number of width units | 6 |

Connection

| | |
|---------------------|------------------------|
| Connector/plug type | DRA (DIN-rail Adapter) |
|---------------------|------------------------|

Texts

| | |
|--------------------|--|
| Encoding | Management of 4 configurable user profiles |
| Labelling | With labelling field |
| Voltage | Power supply via PoE or 24 V DC |
| Installation mode | For installation in distribution box |
| Connectors jacks | With 2 USB jacks type B, USB 2.0 compliant |
| Type of connection | With quickconnect plug-in terminals |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|