



TJA670



Domovea basic

Technical Features

Equipment

Web server Yes

Voltage

Operating voltage 24 - 24 V

Operating voltage over bus 21 - 32 V

Type voltage supply DC

Connectivity

Type of interface bus system/media gateway Multiple interface

Settings

Supported configuration mode ETS
easy

Safety

Ingress Protection (IP) class IP20

Equipment

Number of channels 1

Use conditions

Operating temperature -5 - 45 °C

Controls and indicators

With LED indication Yes

Dimensions

Width 105 mm

Dimensions 90 x 105 mm

Depth 65 mm

Number of width units 6

Connection

Connector/plug type DRA (DIN-rail Adapter)

Texts

Encoding Management of 4 configurable user profiles

Labelling With labelling field

Voltage Power supply via PoE or 24 V DC

Installation mode For installation in distribution box

Connectors jacks With 2 USB jacks type B, USB 2.0 compliant

Type of connection With quickconnect plug-in terminals

Sustainability

RoHS conform Yes