



TJA670



### Domovea basic

#### Technical Features

##### Equipment

Web server	Yes
------------	-----

##### Voltage

Operating voltage	24 - 24 V
Operating voltage over bus	21 - 32 V
Type voltage supply	DC

##### Connectivity

Type of interface bus system/media gateway	Multiple interface
--	--------------------

##### Settings

Supported configuration mode	ETS easy
------------------------------	-------------

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Equipment

Number of channels	1
--------------------	---

##### Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

##### Controls and indicators

With LED indication	Yes
---------------------	-----

##### Dimensions

Width	105 mm
Dimensions	90 x 105 mm
Depth	65 mm
Number of width units	6

##### Connection

Connector/plug type	DRA (DIN-rail Adapter)
---------------------	------------------------

##### Texts

Encoding	Management of 4 configurable user profiles
Labelling	With labelling field
Voltage	Power supply via PoE or 24 V DC
Installation mode	For installation in distribution box
Connectors jacks	With 2 USB jacks type B, USB 2.0 compliant
Type of connection	With quickconnect plug-in terminals

##### Sustainability

RoHS conform	Yes
--------------	-----