



TJA670



**Domovea basic**

**Technical Features**

**Equipment**

Web server Yes

**Voltage**

Operating voltage 24 - 24 V

Operating voltage over bus 21 - 32 V

Type voltage supply DC

**Connectivity**

Type of interface bus system/media gateway Multiple interface

**Settings**

Supported configuration mode ETS  
easy

**Safety**

Ingress Protection (IP) class IP20

**Equipment**

Number of channels 1

**Use conditions**

Operating temperature -5 - 45 °C

**Controls and indicators**

With LED indication Yes

**Dimensions**

Width 105 mm

Dimensions 90 x 105 mm

Depth 65 mm

Number of width units 6

**Connection**

Connector/plug type DRA (DIN-rail Adapter)

**Texts**

Encoding Management of 4 configurable user profiles

Labelling With labelling field

Voltage Power supply via PoE or 24 V DC

Installation mode For installation in distribution box

Connectors jacks With 2 USB jacks type B, USB 2.0 compliant

Type of connection With quickconnect plug-in terminals

**Sustainability**

RoHS conform Yes