



TRM691E



Module 1 flush mounted dimmer 200W, 2 wires + 2 inputs, KNX radio

Technical Features

Voltage

System supply voltage	230 V AC
-----------------------	----------

Electric current

Rated current	0.85 A
---------------	--------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Use conditions

Operating temperature	-15 - 45 °C
-----------------------	-------------

Connection

Cross-section flexible conductor	0.5 - 1.5 mm ²
Cross-section rigid conductor	0.5 - 2.5 mm ²

Equipment

Number of outputs	1
-------------------	---

Lighting

LED lamp power	50 W
----------------	------

Equipment

Type of dimmer	Universal
With battery	No

Capacity

Number of modules	0
-------------------	---

Power

Power incandescent lamp	200 - 200 W
Power of variator	200 - 200 W

Connectivity

With bus system KNX radio	Yes
Type of connection	Screw terminal

Settings

Supported configuration mode	quicklink
------------------------------	-----------

Texts

Fuse	Short-circuit and overload-proof (electronic fuse)
Dimming principle	Phase cut-on or cut-off according to load type, self-learning
Function	Reset function (to factory setting)
Type of connection	With screw-in lift terminals

Sustainability

RoHS conform	Yes
--------------	-----