



TRM691E



**Module 1 flush mounted dimmer 200W, 2 wires + 2 inputs, KNX radio**

**Technical Features**

**Voltage**

System supply voltage 230 V AC

**Frequency**

Frequency 50 - 50 Hz

**Use conditions**

Operating temperature -15 - 45 °C

**Connection**

Cross-section flexible conductor 0.5 - 1.5 mm<sup>2</sup>

Cross-section rigid conductor 0.5 - 2.5 mm<sup>2</sup>

**Equipment**

Number of outputs 1

**Lighting**

LED lamp power 50 W

**Equipment**

Type of dimmer Universal

**Capacity**

Number of modules 0

**Power**

Power incandescent lamp 200 - 200 W

Power of variator 200 - 200 W

**Connectivity**

With bus system KNX radio Yes

Type of connection Screw terminal

**Settings**

Supported configuration mode quicklink

**Texts**

Fuse Short-circuit and overload-proof (electronic fuse)

Dimming principle Phase cut-on or cut-off according to load type, self-learning

Function Reset function (to factory setting)

Type of connection With screw-in lift terminals

**Sustainability**

RoHS conform Yes