



TRM691E



Module 1 flush mounted dimmer 200W, 2 wires + 2 inputs, KNX radio

Technical Features

Voltage

System supply voltage 230 V AC

Frequency

Frequency 50 - 50 Hz

Use conditions

Operating temperature -15 - 45 °C

Connection

Cross-section flexible conductor 0.5 - 1.5 mm²

Cross-section rigid conductor 0.5 - 2.5 mm²

Equipment

Number of outputs 1

Lighting

LED lamp power 50 W

Equipment

Type of dimmer Universal

Capacity

Number of modules 0

Power

Power incandescent lamp 200 - 200 W

Power of variator 200 - 200 W

Connectivity

With bus system KNX radio Yes

Type of connection Screw terminal

Settings

Supported configuration mode quicklink

Texts

Fuse Short-circuit and overload-proof (electronic fuse)

Dimming principle Phase cut-on or cut-off according to load type, self-learning

Function Reset function (to factory setting)

Type of connection With screw-in lift terminals

Sustainability

RoHS conform Yes