



TYM632C



OUTPUT DEVICE FOR 12 SHUTTERS / BLINDS 230V~ 4A

Technical Features

Settings

Supported configuration mode	ETS
------------------------------	-----

Connectivity

With bus system KNX radio	No
---------------------------	----

Installation, mounting

Mounting on	DIN rail
-------------	----------

Materials

Colour	Light grey
--------	------------

Equipment

With switch for manual switch	Yes
-------------------------------	-----

Electric current

Rated current	4 A
---------------	-----

Max. switching current	4 A
------------------------	-----

Voltage

Operating voltage over bus	21 - 32 V
----------------------------	-----------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Connection

Cross-section flexible conductor	0.5 - 6 mm ²
----------------------------------	-------------------------

Cross-section rigid conductor	0.5 - 6 mm ²
-------------------------------	-------------------------

Capacity

Number of modules	10
-------------------	----

Texts

Function	With safety functions e.g. for wind, rain, alarm With positioning function for blind and lamella position With sun shade function
----------	---

Type of connection	With screw terminals
--------------------	----------------------

Operating mode	Operating mode can be set for roller shutter/awning
----------------	---

Sustainability

RoHS conform	Yes
--------------	-----