




80164774



Push-button 4gang, lab. field, + RGB LED, internal temp. sensor, KNX - K.5, al.

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Electric current

Bus current consumption data transfer	20 mA
---------------------------------------	-------

Functions

With room temperature controller	Yes
----------------------------------	-----

Dimensions

Height	25 mm
Width	66.80 mm
Depth	14.35 mm

Equipment

Number of actuation points	8
----------------------------	---

Controls and indicators

With LED indication	Yes
---------------------	-----

Materials

Colour	Aluminium
RAL code	9006
Material	Thermoplastic
Surface finish	Matt

Accessories

Has labelling field	Yes
---------------------	-----

Screen

With display	No
--------------	----

Texts

Function	Function for manual interruption of automatic functions already triggered
Protection	With dismantling protection
Temperature	Integrated temperature sensor with output of the measured values via object

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes