



80163773



IP20



Push-button 3gang, lab. field,+RGB LED, int. temp. sensor, KNX-K.5, stainl.steel

Technical Features

Installation, mounting

Mounting on Flush mounting

Use conditions

Operating temperature -5 - 45 °C

Electric current

Bus current consumption data transfer 20 mA

Functions

With room temperature controller Yes

Dimensions

Height 15.70 mm

Width 66 mm

Depth 14.35 mm

Equipment

Number of actuation points 6

Controls and indicators

With LED indication Yes

Materials

Colour Stainless steel

RAL code 9022

Material Stainless steel
Thermoplastic

Surface finish Matt

Accessories

Has labelling field Yes

Screen

With display No

Texts

Function Function for manual interruption of automatic functions already triggered

Protection With dismantling protection

Temperature Integrated temperature sensor with output of the measured values via object

Sustainability

REACH-SVHC free Yes

RoHS conform Yes