



80162773



IP20



**Push-button 2gang, + RGB LED, internal temp. sensor, KNX - K.5, stainless steel**

**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Use conditions**

Operating temperature -5 - 45 °C

**Electric current**

Bus current consumption data transfer 20 mA

**Functions**

With room temperature controller Yes

**Dimensions**

Height 25 mm

Width 66.80 mm

Depth 14.35 mm

**Equipment**

Number of actuation points 4

**Controls and indicators**

With LED indication Yes

**Materials**

Colour Stainless steel

RAL code 9022

Material Stainless steel  
Thermoplastic

Surface finish Matt

**Accessories**

Has labelling field Yes

**Screen**

With display No

**Texts**

Function Function for manual interruption of automatic functions already triggered

Protection With dismantling protection

Temperature Integrated temperature sensor with output of the measured values via object

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes