



51733525

Insert of LEDsignal light, white lighting surface-mtd/flush-mtd, W.1, grey matt

Technical Features

Voltage

Rated voltage 230 V

Frequency

Frequency 50 - 60 Hz

Lighting

Type of lamp LED

Materials

Colour Grey

RAL code 7011

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Dimensions

Height 71 mm

Width 71 mm

Depth 48 mm

Connectivity

Mounting type Screw mounting

Safety

Ingress Protection (IP) class IP55

Use conditions

Operating temperature -15 - 30 °C

Texts

Imprint Without imprint

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes