



51733515



Insert of LED signal, red/green lighting surf.-mtd/flush-mtd, W.1, grey matt

Technical Features

Voltage

Rated voltage	230 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Lighting

Type of lamp	LED
--------------	-----

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	71 mm
Width	71 mm
Depth	48 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Safety

Ingress Protection (IP) class	IP55
-------------------------------	------

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Lighting	Homogenous illumination of the separately switchable red and green halves via isolated input terminals
Imprint	Without imprint

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes