



11963532

Stereo loudspeaker conn.boxes-insert hinged cover surf./flushmtd,labfield,W1

Technical Features

Connection

Connector/plug type	Loudspeaker socket
Conductor cross-section	2.50 - 2.50 mm ²

Materials

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	70 mm
Width	70 mm
Depth	51 mm
Built-in depth flush-mounted boxes	35 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Equipment

Shielded	No
With dust cover	Yes

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Outlet	With straight outlet
Labelling	With 2 labelling fields
Supporting plate/supporting ring	With supporting plate

Suitable for

W.1	
-----	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes