



TXA310



Binary input 10 fold, 230V~, modular, KNX

Technical Features

Architecture

Bus system EIB

Settings

Supported configuration mode ETS
easy

Electric current

Number of entry circuits 10

Equipment

External signal voltage necessary No

Connectivity

With bus system KNX radio No

Equipment

Radio frequency bidirectional No

With battery No

With HVAC control No

Installation, mounting

Mounting on DIN rail

Lighting

LED controlling No

Materials

Material Plastic

Colour Light grey

RAL code 7035

Safety

Ingress Protection (IP) class IP20

Use conditions

Operating temperature 0 - 45 °C

Voltage

Input voltage 230 - 230 V

Operating voltage over bus 21 - 32 V

Type voltage supply AC

Dimensions

Length 70 mm

Height 90 mm

Depth 60 mm

Texts

Type of connection With quickconnect plug-in terminals

Sustainability

RoHS conform Yes