



TXA310



Binary input 10 fold, 230V~, modular, KNX

**Technical Features**

**Architecture**

Bus system EIB

**Settings**

Supported configuration mode ETS  
easy

**Electric current**

Number of entry circuits 10

**Equipment**

External signal voltage necessary No

**Connectivity**

With bus system KNX radio No

**Equipment**

Radio frequency bidirectional No

With battery No

With HVAC control No

**Installation, mounting**

Mounting on DIN rail

**Lighting**

LED controlling No

**Materials**

Material Plastic

Colour Light grey

RAL code 7035

**Safety**

Ingress Protection (IP) class IP20

**Use conditions**

Operating temperature 0 - 45 °C

**Voltage**

Input voltage 230 - 230 V

Operating voltage over bus 21 - 32 V

Type voltage supply AC

**Dimensions**

Length 70 mm

Height 90 mm

Depth 60 mm

**Texts**

Type of connection With quickconnect plug-in terminals

**Sustainability**

RoHS conform Yes