



EEN100



Twilight switch 1 channel, 1M, wall mounted cell

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated operational voltage U _e	230 - 230 V
--	-------------

Settings

Switch on delay time	60 s
----------------------	------

Use conditions

Operating temperature	-5 - +45 °C
-----------------------	-------------

Storage/transport temperature	-25 - +70 °C
-------------------------------	--------------

Connection

Cross-section flexible conductor	1.5 - 6 mm ²
----------------------------------	-------------------------

Cross-section rigid conductor	1.5 - 6 mm ²
-------------------------------	-------------------------

Capacity

Number of modules	1
-------------------	---

Texts

Installation mode	For mounting on DIN rail Extension sensor for wall and ceiling mounting
-------------------	--

Type of connection	With screw terminals
--------------------	----------------------

Electric current

Switching current	10 A
-------------------	------

Dimensions

Height	83 mm
--------	-------

Width	17.80 mm
-------	----------

Depth	65 mm
-------	-------

Sustainability

RoHS conform	Yes
--------------	-----