



TRM702A



**Binary 2 inputs device flush mounted battery powered KNX RF**

**Technical Features**

**Settings**

Supported configuration mode	ETS easy quicklink
------------------------------	--------------------------

**Electric current**

Number of entry circuits	2
--------------------------	---

**Equipment**

External signal voltage necessary	No
-----------------------------------	----

**Connectivity**

With bus system KNX radio	Yes
---------------------------	-----

**Equipment**

Radio frequency bidirectional	Yes
With battery	Yes
With HVAC control	No

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Lighting**

LED controlling	No
-----------------	----

**Materials**

Material	Plastic
Colour	Light grey
RAL code	7035

**Safety**

Ingress Protection (IP) class	IP30
-------------------------------	------

**Use conditions**

Operating temperature	-10 - 50 °C
-----------------------	-------------

**Cable**

Cable length	0.20 m
--------------	--------

**Voltage**

Input voltage	3 - 3 V
Type voltage supply	DC
System supply voltage	3 V

**Dimensions**

Height	39 mm
Depth	11 mm

**Texts**

Installation mode	For installation behind flush-mounted inserts
-------------------	---

**Sustainability**

RoHS conform	Yes
--------------	-----