




TRM702A



Binary 2 inputs device flush mounted battery powered KNX RF

Technical Features

Settings

Supported configuration mode	ETS easy quicklink
------------------------------	--------------------------

Electric current

Number of entry circuits	2
--------------------------	---

Equipment

External signal voltage necessary	No
-----------------------------------	----

Connectivity

With bus system KNX radio	Yes
---------------------------	-----

Equipment

Radio frequency bidirectional	Yes
With battery	Yes
With HVAC control	No

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Lighting

LED controlling	No
-----------------	----

Materials

Material	Plastic
Colour	Light grey
RAL code	7035

Safety

Ingress Protection (IP) class	IP30
-------------------------------	------

Use conditions

Operating temperature	-10 - 50 °C
-----------------------	-------------

Cable

Cable length	0.20 m
--------------	--------

Voltage

Input voltage	3 - 3 V
Type voltage supply	DC
System supply voltage	3 V

Dimensions

Height	39 mm
Depth	11 mm

Texts

Installation mode	For installation behind flush-mounted inserts
-------------------	---

Sustainability

RoHS conform	Yes
--------------	-----