



TYA606C



Output module 6x 16A /230V~, KNX

Technical Features

Settings

Supported configuration mode

ETS

Connectivity

With bus system KNX

Yes

With bus system KNX radio

No

Dimensions

Height

90 mm

Depth

65 mm

Number of width units

4

Electric current

Rated current

16 A

Materials

Colour

Light grey

Equipment

Radio frequency bidirectional

No

With switch for manual switch

Yes

Electric current

Bus current consumption while idle

3 mA

Frequency

Frequency

50 - 60 Hz

Power

Power incandescent lamp 230 V

2300 - 2300 W

Output power

2300 W

230 V incandescent and halogen lamp

2300 W

Voltage

Rated operational voltage Ue

230 - 230 V

System supply voltage

30 V DC Via bus

Operating voltage over bus

21 - 32 V

Safety

Ingress Protection (IP) class

IP20

Use conditions

Operating temperature

-5 - 45 °C

Connection

Cross-section rigid conductor

0.75 - 2.5 mm²

Cross-section flexible conductor

0.75 - 2.5 mm²

Texts

Function

With safety functions e.g. for wind, rain, alarm
With positioning function for blind and lamella position
With sun shade function

Type of connection

With quickconnect plug-in terminals

Sustainability

RoHS conform

Yes