



11963512

**Stereo loudspeaker connector box hinged cover surf.-mtd,lab.field,W.1,p.wh.**

**Technical Features**

**Connection**

Connector/plug type	Loudspeaker socket
Conductor cross-section	2.50 - 2.50 mm <sup>2</sup>

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

**Dimensions**

Height	76 mm
Width	76 mm
Depth	65 mm
Built-in depth flush-mounted boxes	35 mm

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Equipment**

Shielded	No
With dust cover	Yes

**Safety**

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

**Use conditions**

Operating temperature	-40 - 30 °C
-----------------------	-------------

**Texts**

Outlet	With straight outlet
Labelling	With 2 labelling fields

**Suitable for**

W.1	
-----	--

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes