




80660100



KNX room cont., colourdisplay, intg bus coupling unit, KNX

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Electric current

Bus current consumption data transfer	10 mA
---------------------------------------	-------

Dimensions

Built-in depth	32 mm
Built-in depth flush-mounted boxes	26 mm
Height	71 mm
Width	71 mm
Depth	46.70 mm

Equipment

Number of actuation points	3
----------------------------	---

Controls and indicators

With LED indication	Yes
---------------------	-----

Materials

Colour	Black
RAL code	9005
Material	Thermoplastic

Screen

With display	Yes
--------------	-----

Texts

Function	With keylock With holiday switching With frost protection function
Installation mode	With spreader claws For flush-mounted and hollow wall mounting For single mounting For vertical mounting
Temperature	Additional connection for external temperature sensor Comfort, standard and night temperature Temperature measurement via internal and/or connectable Temperature sensor with average determination

Sustainability

RoHS conform	Yes
--------------	-----