




EEN101



Twilight switch 1 channel, 1M, flush mounted cell

Technical Features

Frequency

Frequency 50 - 60 Hz

Voltage

Rated operational voltage Ue 230 - 230 V

Settings

Switch on delay time 60 s

Use conditions

Operating temperature -5 - +45 °C

Storage/transport temperature -25 - +70 °C

Connection

Cross-section flexible conductor 1.5 - 6 mm²

Cross-section rigid conductor 1.5 - 6 mm²

Capacity

Number of modules 1

Texts

Installation mode For mounting on DIN rail
Extension sensor for wall and ceiling mounting

Type of connection With screw terminals

Electric current

Switching current 10 A

Dimensions

Height 83 mm

Width 17.80 mm

Depth 65 mm

Sustainability

RoHS conform Yes