



EEN101



Twilight switch 1 channel, 1M, flush mounted cell

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated operational voltage U _e	230 - 230 V
--	-------------

Settings

Switch on delay time	60 s
----------------------	------

Use conditions

Operating temperature	-5 - +45 °C
Storage/transport temperature	-25 - +70 °C

Connection

Cross-section flexible conductor	1.5 - 6 mm ²
Cross-section rigid conductor	1.5 - 6 mm ²

Capacity

Number of modules	1
-------------------	---

Texts

Installation mode	For mounting on DIN rail Extension sensor for wall and ceiling mounting
Type of connection	With screw terminals

Electric current

Switching current	10 A
-------------------	------

Dimensions

Height	83 mm
Width	17.80 mm
Depth	65 mm

Sustainability

RoHS conform	Yes
--------------	-----