




80262280



**S.x KNX (TP+EASY) Movement detector module 2,20m**

**Technical Features**

**Dimensions**

Recommended installation height	2.20 - 2.20 m
---------------------------------	---------------

**Settings**

Supported configuration mode	ETS easy
Minimal duty cycle	10 s

**Functions**

Maximal duty cycle	30 min
--------------------	--------

**Connectivity**

With bus system KNX radio	No
---------------------------	----

**Voltage**

Operating voltage over bus	21 - 32 V
----------------------------	-----------

**Scope of delivery**

Bus connection included	Yes
-------------------------	-----

**Electric current**

Bus current consumption data transfer	10 mA
---------------------------------------	-------

**Lighting**

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

**Detection**

Detection angle adjustable	45 - 90 °
Detection angle horizontal	90 - 180

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Materials**

Material	Metal Plastic
----------	------------------

**Texts**

Push button	With button for automatic/permanent ON/permanent OFF
Operating mode	With 3 operating modes: automatic/permanent ON/permanent OFF
Function	Presence simulation With party function
Installation mode	With spreader claws With dismantling protection

**Sustainability**

RoHS conform	Yes
--------------	-----