



TYM646R



IP20

Heating actuator 6 channels KNX, with regulation, 24/230V

Technical Features

Connectivity

With bus system KNX radio	No
---------------------------	----

Voltage

Operating voltage over bus	21 - 32 V
Output voltage	24 - 230 V
Auxiliary tension	110 - 230 V

Power

Power consumption during operation	1 VA
Power consumption standby	0.40 W

Electric current

Max. switching current	0.16 A
------------------------	--------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Connection

Cross-section flexible conductor	0.5 - 4 mm ²
Cross-section rigid conductor	0.5 - 4 mm ²

Dimensions

Number of width units	4
-----------------------	---

Texts

Function	Blocking function can be activated per actuator output via manual operation buttons or bus With valve protection function
Fuse	Short-circuit proof and overload-proof (display using LEDs)
Type of connection	With screw terminals

Sustainability

RoHS conform	Yes
--------------	-----