



80262170



K.x/Q.x KNX (TP+EASY) Movement detector module 1,10m

Technical Features

Dimensions

Recommended installation height 1.10 - 1.10 m

Settings

Supported configuration mode ETS
easy
Minimal duty cycle 10 s

Functions

Maximal duty cycle 30 min

Connectivity

With bus system KNX radio No

Voltage

Operating voltage over bus 21 - 32 V

Scope of delivery

Bus connection included Yes

Electric current

Bus current consumption data transfer 10 mA

Lighting

Response brightness adjustable 5 - 1000 lx

Detection

Detection angle adjustable 45 - 90 °

Detection angle horizontal 90 - 180

Use conditions

Operating temperature -5 - 45 °C

Materials

Material Metal
Plastic

Texts

Push button With button for automatic/permanent ON/permanent OFF

Operating mode With test mode
Master/slave operation for covering large detection areas
With 3 operating modes: automatic/permanent ON/permanent OFF

Function Presence simulation
With party function

Installation mode With spreader claws
With dismantling protection

Sustainability

RoHS conform Yes