



HTC310H

COMMUNICATION Module without inputs and outputs

Technical Features

Use conditions

Operating temperature	-25 - 70 °C
Storage/transport temperature	-35 - 70 °C

Connectivity

With bus system KNX radio	No
---------------------------	----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Capacity

Number of modules	2
-------------------	---

Voltage

Type voltage supply	DC
Operating voltage	24 - 24 V

Connection

Cross-section digital output	1.50 - 1.50 mm ²
Cross-section digital input	1.50 - 1.50 mm ²

Installation, mounting

Mounting on	DIN rail
-------------	----------

Sustainability

RoHS conform	Yes
--------------	-----