



KDN180G

Insulated busbar 1P 80A fork 16mm² 18M

Technical Features

Electric current

| | |
|---------------|------|
| Rated current | 80 A |
|---------------|------|

Architecture

| | |
|-----------------|---|
| Number of poles | 1 |
|-----------------|---|

Dimensions

| | |
|--------|--------|
| Length | 319 mm |
|--------|--------|

Voltage

| | |
|--|-------------|
| Rated impulse withstand voltage U _{imp} | 4000 V |
| Rated operational voltage U _e | 415 - 415 V |

Connection

| | |
|-------------------------------|------------------------|
| Cross-section rigid conductor | 16 mm ² |
| Connector/plug type | Phase busbar with fork |

Capacity

| | |
|-------------------|----|
| Number of modules | 18 |
|-------------------|----|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|