



6765102089



Soc.out. earth.pin+LED orient.,enhncd contact prot.,screw-in lift ,1930/R.cl,wh

#### Technical Features

##### Electric current

Rated current	16 A
---------------	------

##### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

##### Dimensions

Height	71 mm
Width	71 mm
Depth	42 mm

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting Claw mounting

##### Equipment

Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	No
With round protective earth pin	Yes
With signal lamp	No
With lock	No

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	1
-------------------	---

##### Controls and indicators

Type of lighting for the installation devices	Integrated orientation light
---	------------------------------

##### Safety

With enhanced contact protection	Yes
Ingress Protection (IP) class	IP20

##### Functions

With orientation lighting	Yes
With function lighting	No

##### Texts

Imprint	Without imprint
Cover	Central cover plate
Lighting	Additional benefit by combination of a socket outlet with an orientation light
Wiring	Through-wiring possible, therefore also ideal for retrofitting

<b>Texts</b>	
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals
<b>Suitable for</b>	
R.x	
<b>Sustainability</b>	
RoHS conform	Yes