



6765098914



Soc.out. earth.pin+LED,enhncd contact prot.,screw-in lift term.,S1/B3/7,orange

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Orange
RAL code 2003
Surface finish Glossy
Material Duroplastic
Treatment Untreated

Dimensions

Height 71 mm
Width 71 mm
Depth 41.60 mm
Built-in depth flush-mounted boxes 31 mm
Built-in depth 32 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal
Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet Earthing pin
Rotated central insert No
With hinged lid No
With round protective earth pin Yes
With signal lamp No
With lock No

Accessories

Has labelling field No

Capacity

Number of modules 1

Controls and indicators

Type of lighting for the installation devices Integrated operating control light

Safety

With enhanced contact protection Yes
Ingress Protection (IP) class IP20

Functions

With orientation lighting No
With function lighting Yes

Texts

Imprint Without imprint
Cover Central cover plate

Texts

Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

Suitable for

S.x/B.x

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes