



80141500



IP55



Group push-button mod. 2gang surface-/flush-mounted, BCU, KNX-W.1, grey gl./matt

**Technical Features**

**Installation, mounting**

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

**Use conditions**

Operating temperature	-40 - 30 °C
-----------------------	-------------

**Electric current**

Bus current consumption data transfer	10 mA
---------------------------------------	-------

**Functions**

With room temperature controller	No
----------------------------------	----

**Dimensions**

Built-in depth	22 mm
Built-in depth flush-mounted boxes	32 mm
Height	44 mm
Width	45.70 mm
Depth	40.50 mm

**Equipment**

Number of actuation points	4
----------------------------	---

**Controls and indicators**

With LED indication	Yes
---------------------	-----

**Materials**

Colour	Grey
RAL code	7011 7035
Material	Duroplastic
Surface finish	Glossy Matt

**Accessories**

Has labelling field	No
---------------------	----

**Screen**

With display	No
--------------	----

**Texts**

Function	Function for manual interruption of automatic functions already triggered
----------	---

**Sustainability**

RoHS conform	Yes
--------------	-----