



80141300



Group push-button mod. 1gang surface-/flush-mounted, BCU, KNX-W.1, grey gl./matt

Technical Features

Installation, mounting

| | |
|-------------|------------------------------------|
| Mounting on | Flush mounting Surface mounting |
|-------------|------------------------------------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -40 - 30 °C |
|-----------------------|-------------|

Electric current

| | |
|---------------------------------------|-------|
| Bus current consumption data transfer | 10 mA |
|---------------------------------------|-------|

Functions

| | |
|----------------------------------|----|
| With room temperature controller | No |
|----------------------------------|----|

Dimensions

| | |
|------------------------------------|----------|
| Built-in depth | 22 mm |
| Built-in depth flush-mounted boxes | 32 mm |
| Height | 44 mm |
| Width | 45.70 mm |
| Depth | 40.50 mm |

Equipment

| | |
|----------------------------|---|
| Number of actuation points | 2 |
|----------------------------|---|

Controls and indicators

| | |
|---------------------|-----|
| With LED indication | Yes |
|---------------------|-----|

Materials

| | |
|----------------|----------------|
| Colour | Grey |
| RAL code | 7011 7035 |
| Material | Duroplastic |
| Surface finish | Glossy Matt |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Screen

| | |
|--------------|----|
| With display | No |
|--------------|----|

Texts

| | |
|----------|---|
| Function | Function for manual interruption of automatic functions already triggered |
|----------|---|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|