



EG103V



**Weekly time switch 1 channel, 12/24V, digital, 2 modules**

**Technical Features**

**Voltage**

Rated operational voltage U<sub>e</sub> 12 - 24 V

**Frequency**

Frequency 50 - 60 Hz

**Power**

230 V incandescent and halogen lamp 2300 W

**Functions**

Power reserve in years 5 y  
 With network synchronisation No  
 With quartz synchronisation Yes  
 Number of function channels 1

**Equipment**

Accuracy per day 1.5 s  
 With impulse programme Yes  
 Number of channels 1

**Connection**

Type of contacts 1x changeover

**Settings**

Daily programme Yes  
 Weekly programme No  
 Annual programme No

**Use conditions**

Operating temperature -5 - +45 °C

**Connection**

Cross-section flexible conductor 1 - 16 mm<sup>2</sup>  
 Cross-section rigid conductor 1 - 6 mm<sup>2</sup>

**Texts**

Type of connection With screw terminals  
 Function Keylock by means of blocking key  
 With pulse function

**Dimensions**

Height 85 mm  
 Width 35 mm  
 Depth 64 mm

**Main electrical attributes**

Minimum interval between 2 switching times 1 min

**Capacity**

Number of modules 2