



EG103V



Weekly time switch 1 channel, 12/24V, digital, 2 modules

Technical Features

Voltage

Rated operational voltage U_e 12 - 24 V

Frequency

Frequency 50 - 60 Hz

Power

230 V incandescent and halogen lamp 2300 W

Functions

Power reserve in years 5 y
 With network synchronisation No
 With quartz synchronisation Yes
 Number of function channels 1

Equipment

Accuracy per day 1.5 s
 With impulse programme Yes
 Number of channels 1

Connection

Type of contacts 1x changeover

Settings

Daily programme Yes
 Weekly programme No
 Annual programme No

Use conditions

Operating temperature -5 - +45 °C

Connection

Cross-section flexible conductor 1 - 16 mm²
 Cross-section rigid conductor 1 - 6 mm²

Texts

Type of connection With screw terminals
 Function Keylock by means of blocking key
 With pulse function

Dimensions

Height 85 mm
 Width 35 mm
 Depth 64 mm

Main electrical attributes

Minimum interval between 2 switching times 1 min

Capacity

Number of modules 2