



EG103D



**Radio-synchronized 1 channel digital time switch weekly cycle, Evolution**

**Technical Features**

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Power**

230 V incandescent and halogen lamp	2300 W
-------------------------------------	--------

**Functions**

Power reserve in years	5 y
With network synchronisation	No
With quartz synchronisation	Yes
Number of function channels	1

**Equipment**

With impulse programme	Yes
Number of channels	1

**Connection**

Type of contacts	1x changeover
------------------	---------------

**Settings**

Daily programme	No
Weekly programme	Yes
Annual programme	No

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Connection**

Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>

**Texts**

Type of connection	With screw terminals
Function	Keylock by means of blocking key With pulse function Presence simulation

**Dimensions**

Height	85 mm
Width	35 mm
Depth	64 mm

**Main electrical attributes**

Minimum interval between 2 switching times	1 min
--	-------

**Capacity**

Number of modules	2
-------------------	---