

**Push Switch Wide Rocker Grey Marked 'FAN BOOST'**

**Technical Features**

**Electric current**

Switching current	10 A
Momentary contact current	10 A

**Voltage**

Rated voltage	250 V
---------------	-------

**Architecture**

Number of poles	2
-----------------	---

**Materials**

Colour	Grey
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Coated
Transparent	No

**Dimensions**

Height	86 mm
Width	86 mm
Depth	24 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Controls and indicators**

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Accessories**

Has labelling field	No
---------------------	----

**Texts**

Imprint	Without imprint
Installation mode	For flush-mounted and hollow wall mounting
Switch mode	NO contact

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes