



WNA160B



IP55



cubyko Schuko Socket composable white IP55

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Use conditions

Operating temperature -15 - 30 °C

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white
RAL code 9010
Surface finish Matt
Material Thermoplastic
Treatment Untreated

Dimensions

Height 71 mm
Width 71 mm
Depth 22.80 mm
Number of units 1
Built-in depth flush-mounted boxes 0 mm

Connection

Connector/plug type Turn screw lock
Cross-section flexible conductor without wire end sleeve 1.0 - 2.5 mm²

Installation, mounting

Mounting on Flush mounting
Surface mounting
Mounting-/Connection Position Horizontal

Connectivity

Type of connection Plug-in connection
Mounting type Screw mounting

Equipment

Connector/plug type socket outlet SCHUKO
Rotated central insert No
With hinged lid Yes
With round protective earth pin No
With signal lamp No
With lock No

Accessories

Has labelling field No
Pre-equipped with Socket outlet

Cover, door

Type of lid Self-closing hinged cover, can be arrested in end position

Capacity

Number of modules 1

Safety

With enhanced contact protection Yes
Impact resistance IK IK05

Safety

| | |
|-------------------------------|------------------------|
| Ingress Protection (IP) class | IP55 |
| Usable in higher IP class | IP55 with closed cover |

Functions

| | |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting | No |

Identification

| | |
|--------------|----|
| With imprint | No |
|--------------|----|

Texts

| | |
|--------------------|-----------------------------|
| Cover | Complete housing |
| Protection | Enhanced contact protection |
| Type of connection | With plug-in terminals |
| Labelling | Without labelling |

Suitable for

| | |
|--------|--|
| cubyko | |
|--------|--|

Sustainability

| | |
|--------------|-----|
| Halogen free | Yes |
| RoHS conform | Yes |