



WNA401

**cubyko Single flush adapter composable grey IP55**

**Technical Features**

**Capacity**

Number of gangs	1
Number of modules	1

**Materials**

Colour	Light grey
RAL code	7035
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

**Dimensions**

Height	83 mm
Width	83 mm
Depth	39 mm
Number of units horizontal	1
Number of units vertical	1

**Accessories**

Has labelling field	No
---------------------	----

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

**Use conditions**

Operating temperature	-15 - 30 °C
-----------------------	-------------

**Texts**

Installation mode	With clamp/screw fastening With mounting adapter and sealing For flush-mounted and hollow wall mounting
-------------------	---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes