



WNA408B

cubyko Double vertical flush adapter white IP55

Technical Features

Capacity

Number of gangs	2
-----------------	---

Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy Mat
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	87 mm
Width	293.50 mm
Depth	9.90 mm
Number of units horizontal	1
Number of units vertical	2

Accessories

Has labelling field	No
---------------------	----

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Installation mode	With mounting adapter and sealing For flush-mounted and hollow wall mounting For vertical mounting
-------------------	--

Sustainability

Halogen free	Yes
REACH conform	Yes
RoHS conform	Yes