



WNA037B



cubyko Key switch 3 positions non stable composable white IP55

Technical Features

Materials

Colour	Polar white
RAL code	9010

Controls and indicators

Venetian blind switch type	1-pole switch
----------------------------	---------------

Materials

Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Electric current

Switching current	10 A
Switching current	10 A

Safety

Ingress Protection (IP) class	IP55
-------------------------------	------

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Switch mode	1-pole
Type of connection	With screw terminals
Installation mode	For screw fastening
Terminal	With Wago clip-in 2-wire connection terminal for wiring With two clip-in places for Wago 2-wire connection terminals in the housing floor Isolated input terminals for UP and DOWN
Function	With push lock function

Connection

Connector/plug type	Turn screw lock
---------------------	-----------------

Suitable for

cubyko	
--------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes