



WNE100B

cubyko Socket 2P+E screwless flush mounted white IP55

Technical Features

Electric current

Rated current	16 A
---------------	------

Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Pure white
RAL code	9010
Surface finish	Satin finish
Material	Polycarbonate (PC)
Treatment	Varnished

Dimensions

Height	75 mm
Width	75 mm
Depth	22.80 mm
Built-in depth flush-mounted boxes	40 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	French norm NF
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	Yes
With signal lamp	No

Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

Capacity

Number of modules	2
-------------------	---

Safety

With enhanced contact protection	No
Impact resistance IK	IK07
Ingress Protection (IP) class	IP55

Functions

With orientation lighting	No
---------------------------	----

Texts

Imprint	With imprint
Cover	For covering of socket outlets
Protection	Without protective screen

Suitable for

Hager cubyko	
--------------	--

Sustainability

Halogen free	Yes
RoHS conform	Yes