



WNA035

**cubyko Key switch 2 positions composable grey IP55**

**Technical Features**

**Installation, mounting**

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Grey
RAL code	7011
Surface finish	Satin finish
Material	Polypropylene (PP)
Treatment	Varnished

**Identification**

Assembly arrangement	Mechanism with upper casing
----------------------	-----------------------------

**Connectivity**

Mounting type	Click mounting
---------------	----------------

**Controls and indicators**

Number of buttons	1
-------------------	---

**Dimensions**

Dimensions	75 x 75 mm
Built-in depth flush-mounted boxes	40 mm

**Safety**

Impact resistance IK	IK07
----------------------	------

**Electric current**

Rated current	10 A
---------------	------

**Connection**

Connector/plug type	Turn screw lock
---------------------	-----------------

**Texts**

Lighting	Without lighting (cannot be illuminated)
----------	--

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes