



WNA403

cubyko Triple horizontal flush adapter grey IP55

Technical Features

Capacity

Number of gangs	3
Number of modules	3

Materials

Colour	Grey
RAL code	7035
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	224 mm
Width	83 mm
Depth	38 mm
Number of units horizontal	3
Number of units vertical	1

Accessories

Has labelling field	No
---------------------	----

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Installation mode	With clamp/screw fastening With mounting adapter and sealing For flush-mounted and hollow wall mounting For horizontal mounting
-------------------	------------------------------------------------------------------------------------------------------------------------------------------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes