



WNA160



IP55

cubyko Schuko Socket composable grey IP55

Technical Features

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -15 - 30 °C |
|-----------------------|-------------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Materials

| | |
|----------------|-------------------------------------|
| Colour | Grey |
| RAL code | 7011 |
| Surface finish | Matt |
| Material | Polypropylene (PP) Thermoplastic |
| Treatment | Untreated |

Dimensions

| | |
|------------------------------------|----------|
| Height | 71 mm |
| Width | 71 mm |
| Depth | 22.80 mm |
| Number of units | 1 |
| Built-in depth flush-mounted boxes | 0 mm |

Connection

| | |
|---------------------|-----------------|
| Connector/plug type | Turn screw lock |
|---------------------|-----------------|

Installation, mounting

| | |
|-------------|------------------------------------|
| Mounting on | Flush mounting Surface mounting |
|-------------|------------------------------------|

Connectivity

| | |
|--------------------|--------------------|
| Type of connection | Plug-in connection |
| Mounting type | Screw mounting |

Equipment

| | |
|-----------------------------------|--------|
| Connector/plug type socket outlet | SCHUKO |
| Rotated central insert | No |
| With hinged lid | Yes |
| With round protective earth pin | No |
| With signal lamp | No |
| With lock | No |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Cover, door

| | |
|-------------|--|
| Type of lid | Self-closing hinged cover, can be arrested in end position |
|-------------|--|

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Safety

| | |
|----------------------------------|------|
| With enhanced contact protection | Yes |
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP55 |

Functions

| | |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting | No |

Identification

| | |
|--------------|----|
| With imprint | No |
|--------------|----|

Texts

| | |
|--------------------|-----------------------------|
| Cover | Complete housing |
| Protection | Enhanced contact protection |
| Type of connection | With plug-in terminals |

Suitable for

cubyko

Sustainability

| | |
|--------------|-----|
| Halogen free | Yes |
| RoHS conform | Yes |