



WNA160



cubyko Schuko Socket composable grey IP55

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Rated current	16 A
---------------	------

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Polypropylene (PP) Thermoplastic
Treatment	Untreated
Contains recycled material (% of total plastic weight)	0 %

Dimensions

Height	71 mm
Width	71 mm
Depth	22.80 mm
Number of units	1
Built-in depth flush-mounted boxes	0 mm
Built-in depth	22 mm

Connection

Connector/plug type	Turn screw lock
Cross-section flexible conductor without wire end sleeve	1.0 - 2.5 mm ²

Installation, mounting

Mounting on	Flush mounting Surface mounting
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Plug-in connection
With claw mounting	No
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
Pre-equipped with	Socket outlet

Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

Capacity

Number of modules	1
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP55
Usable in higher IP class	IP55 with closed cover

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Imprint	Without imprint
Cover	Complete housing
Protection	Enhanced contact protection
Type of connection	With plug-in terminals
Labelling	Without labelling

Suitable for

cubyko	
--------	--

Sustainability

Halogen free	Yes
RoHS conform	Yes