



WNA401B

cubyko Single flush adapter composable white IP55

Technical Features

Capacity

| | |
|-------------------|---|
| Number of gangs | 1 |
| Number of modules | 1 |

Materials

| | |
|----------------|---------------|
| Colour | Polar white |
| RAL code | 9010 |
| Surface finish | Matt |
| Material | Thermoplastic |
| Treatment | Untreated |

Dimensions

| | |
|--------|-------|
| Height | 83 mm |
| Width | 83 mm |
| Depth | 39 mm |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Installation, mounting

| | |
|-------------------------------|------------------------|
| Mounting on | Flush mounting |
| Mounting-/Connection Position | Horizontal Vertical |

Safety

| | |
|-------------------------------|------------------------|
| Ingress Protection (IP) class | IP20 |
| Usable in higher IP class | IP55 with closed cover |
| Impact resistance IK | IK05 |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -15 - 30 °C |
|-----------------------|-------------|

Texts

| | |
|-------------------|---|
| Installation mode | With clamp/screw fastening With mounting adapter and sealing For flush-mounted and hollow wall mounting |
|-------------------|---|

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |