



WNE122B

cubyko Double horizontal socket 2P+E screwless flush mounted white IP55

Technical Features

Electric current

Rated current 16 A

Voltage

Nominal voltage 250 - 250 V

Use conditions

Operating temperature -15 - 30 °C

Frequency

Frequency 50 - 60 Hz

Materials

Colour Pure white

RAL code 9010

Surface finish Satin finish

Material Polypropylene (PP)

Treatment Varnished

Dimensions

Height 45 mm

Width 90 mm

Depth 42.50 mm

Built-in depth flush-mounted boxes 40 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Plug-in connection

Mounting type Screw mounting

Equipment

Connector/plug type socket outlet French norm NF

Rotated central insert No

With hinged lid Yes

With round protective earth pin Yes

With signal lamp No

Cover, door

Type of lid Self-closing hinged cover, can be arrested in end position

Capacity

Number of modules 4

Safety

With enhanced contact protection No

Impact resistance IK IK07

Ingress Protection (IP) class IP55

Functions

With orientation lighting No

Texts

Imprint With imprint

Cover For covering of socket outlets

Protection Without protective screen

Suitable for

Hager cubyko

Sustainability

Halogen free	Yes
RoHS conform	Yes
